


Model E15



Unit: mm

Rail length $L (\pm 0.8)$	Stroke $S (\pm 3)$	Mounting hole dimensions $A \pm 0.3$	Permissible load N/pair	Mass [g/pair]
50	20	30	5	15
80	45	60	8	24
100	60	80	10	30
120	75	100	10	36


Note) The Permissible Load and Mass each indicate when used as a pair of 2 units.

Model number coding

E15 +100L

Model number Overall rail length (mm)

Model E20



Unit: mm

Rail length L (± 0.8)	Stroke S (± 3)	Mounting hole dimensions			Permissible load N/pair	Mass [g/pair]
		A ± 0.3	B ± 0.3	n (pcs)		
80	45	50	—	2	20	50
100	60	70	—	2	30	62
150	85	60	120	3	80	98
200	120	85	170	3	140	131
300	180	135	270	3	145	197

Note) The Permissible Load and Mass each indicate when used as a pair of 2 units.

Model number coding

E20 +150L

Model number Overall rail length (mm)